

# Model: HSD-1106-01 1-50%RH, 1160L



HSD-1106-01 has an outstanding performance for drying moisture sensitive components and PCBs as a result of a high performance drying unit. Humidity can be controlled precisely by digital panel to reach the lowest 1%RH. It is specially designed for moisture sensitive SMD packages to comply with IPC/JEDEC J-STD-033D. Two powerful dry units installed, making it very suitable for operation with frequent approach.

Totech (Toyo Living) is the creator of world's first Automatic Drying System invented in 1974.

Super Dry cabinets use the highly-quality and highly reliable Toyo Living engine and has been sold over 700,000 units and used in over 10,000 companies around the world. We also supply various kinds of custom-build cabinet to best suit our client's need.

### Features

- ❖ Modular design: Totech Super Dry is modularly designed dry cabinet. The main modules include dry units, control box, sensor, shelves and castors. All of the modules can be replaced easily. Totech dry cabinet can be used as long as the cabinet structure is in good condition. Most of our customers can use the Totech dry cabinets for more than 10 years without any problem.
- ❖ Dry units: 1%RH
- \* ESD safe: Cabinet is with ESD painted steel body, ESD safe steel shelves and ground wire, well comply with IEC 61340-5-1.
- ❖ Convenient operation: Totech Super Dry cabinet is with digital control panel, can control the humidity precisely from 1% to 50%RH, by adjusting  $\pm 0.1$ %RH. Humidity, temperature and alarm functions are shown and can be adjusted by digital control panel. Key Lock function on the digital control panel prevents unintended changes of setting. Sensor calibration function is also available with digital panel.
- \* Maintenance free: Totech dry cabinet works by dry units. An interlocked fan causes the air to circulate through the dry unit, while passing through the dry unit moisture in the air is absorbed by the zeolite desiccant. During periodic regenerating of the zeolite desiccant by heating, the absorbed humidity is evaporated and exhausted through the external shutters of the dry unit. The process is physical, and no extra maintenance at all.
- ❖ Lockable doors: Every door can be locked separately with a key.
- \* Humidity alarm (Optional): Humidity alarm buzzer / humidity alarm light will sound or flash if the humidity exceeds set value.

SUPER DRY maintains preset internal humidity 1%RH and is ideal for moisture-proof and anti-oxidation storage applications, offering protection from corrosion, mold and deterioration for such items as:

- ❖ All kinds of Integrated Circuits (IC), like Monolithic, BGA, QFP; PLCC, Bipolar etc.
- Silicon Wafers.
- Aerospace related Instruments and Tools.
- Optical Equipment and Machine Tools.
- PDP Inspection Equipment, Liquid Crystal Cleaning Equipment, LCDs, TACs etc.
- . LEDs and LDs.

## **Specifications**


Humidity Range	1%-50%RH
Sensor precision	$\pm$ 2%RH, $\pm$ 1 $^{\circ}$ C
External dimensions	(W x H x D) 1200 x 1840 x 658 mm
Internal dimensions	(W x H x D) 1190 x 1560 x 620 mm
Weight	167 kg
Capacity	1160 L
Shelves (W x D)	5 pcs, adjustable (ESD safe painted steel)
Max weight on shelf	100 kg
Structure	1.2mm steel, ESD safe painted steel
Cabinet color	Gray
Door	6 pcs, with handles, airtight magnetic sealers and tempered glas windows
ESD grounding wire	1Μ Ω
Voltage	AC220 V 50/60Hz (AC110V -240V optional)
Power consumption	Ave. 56W/h
Castors	4 pcs, 2 of them with brakes








# Model: HSD-1106-01 1-50%RH, 1160L



**Unloaded Test** 



**❖** Condition: 2012.08.29 16:40 ~ 2012.08.31 08:00

top view

Instrument: CHINO Data logger, Model: MR6662. Accuracy rating:  $\pm$  0.5° C,  $\pm$ 3%RH.










Model: HSD-1106-01 1-50%RH, 1160L

### **Digital Control Panel**

- Set humidity value precisely, display humidity and temperature value
- Set the humidity and door open alarm
- Set the nitrogen purging time
- Lock the panel to avoid unintended changes of setting
- ❖ Sensor calibration



Available options



◆Extra shelf



❖SMD single rack (stainless steel)



❖SMD double rack (stainless steel)



❖Humidity/ Door open alarm buzzer



❖Humidity alarm light

Greatly increase the usable space inside Super Dry

Suitable for storage of components on tape and reel, can pull out on rail Suitable for storage of components on tape and reel, can pull out on rail

Alarm buzzer sounds when its internal humidity/ door open time exceeds set value

Alarm light flashes and sounds when its internal humidity exceeds set value



❖Independent Nitrogen purge system (Model TN2-02)



❖Nitrogen valve (Model: HN2-01)



❖Nitrogen auto purge system (Model AN2-03)



❖Adjustable legs



❖Wrist strap connection

Effective usage of N<sub>2</sub> combined with Super Dry, help to accelerate the recovery time and oxidation prevention. Set the buttons on N2 purge system itself

Simple N<sub>2</sub> flow meter 0-25L/min adjustable

Effective usage of  $N_2$ combined with Super Dry, help to accelerate the recovery time and oxidation prevention. Set on digital control panel Available for effective stabilization

Allows grounding while handling ESD sensitive materials





\* Data logger with data reader Testo 174H

Record the humidity and temperature data of dry cabinet; data can be output from PC



Castors(4 pcs)

To move the cabinet on floor easily





